

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/17/12	D.GRIFFIN




CHART A								
FPT9OM1-LC-12PK-1			FPT9OM1-LC-12PK-2			FPT9OM1-LC-12PK-3		
PART NUMBER	LENGTH M [FT]	COLOR	PART NUMBER	LENGTH M [FT]	COLOR	PART NUMBER	LENGTH M [FT]	COLOR
FPT9OM1-LC-BLK-1	1.0 [3.28]	BLACK	FPT9OM1-LC-BLK-2	2.0 [6.56]	BLACK	FPT9OM1-LC-BLK-3	3.0 [9.84]	BLACK
FPT9OM1-LC-ORG-1	1.0 [3.28]	ORANGE	FPT9OM1-LC-ORG-2	2.0 [6.56]	ORANGE	FPT9OM1-LC-ORG-3	3.0 [9.84]	ORANGE
FPT9OM1-LC-YLW-1	1.0 [3.28]	YELLOW	FPT9OM1-LC-YLW-2	2.0 [6.56]	YELLOW	FPT9OM1-LC-YLW-3	3.0 [9.84]	YELLOW
FPT9OM1-LC-GRY-1	1.0 [3.28]	GRAY	FPT9OM1-LC-GRY-2	2.0 [6.56]	GRAY	FPT9OM1-LC-GRY-3	3.0 [9.84]	GRAY
FPT9OM1-LC-BLU-1	1.0 [3.28]	BLUE	FPT9OM1-LC-BLU-2	2.0 [6.56]	BLUE	FPT9OM1-LC-BLU-3	3.0 [9.84]	BLUE
FPT9OM1-LC-GRN-1	1.0 [3.28]	GREEN	FPT9OM1-LC-GRN-2	2.0 [6.56]	GREEN	FPT9OM1-LC-GRN-3	3.0 [9.84]	GREEN
FPT9OM1-LC-AQU-1	1.0 [3.28]	AQUA	FPT9OM1-LC-AQU-2	2.0 [6.56]	AQUA	FPT9OM1-LC-AQU-3	3.0 [9.84]	AQUA
FPT9OM1-LC-BRN-1	1.0 [3.28]	BROWN	FPT9OM1-LC-BRN-2	2.0 [6.56]	BROWN	FPT9OM1-LC-BRN-3	3.0 [9.84]	BROWN
FPT9OM1-LC-RED-1	1.0 [3.28]	RED	FPT9OM1-LC-RED-2	2.0 [6.56]	RED	FPT9OM1-LC-RED-3	3.0 [9.84]	RED
FPT9OM1-LC-WHT-1	1.0 [3.28]	WHITE	FPT9OM1-LC-WHT-2	2.0 [6.56]	WHITE	FPT9OM1-LC-WHT-3	3.0 [9.84]	WHITE
FPT9OM1-LC-VIO-1	1.0 [3.28]	VIOLET	FPT9OM1-LC-VIO-2	2.0 [6.56]	VIOLET	FPT9OM1-LC-VIO-3	3.0 [9.84]	VIOLET
FPT9OM1-LC-ROS-1	1.0 [3.28]	ROSE	FPT9OM1-LC-ROS-2	2.0 [6.56]	ROSE	FPT9OM1-LC-ROS-3	3.0 [9.84]	ROSE

NOTES:

- LC CONNECTOR ASSEMBLY POLISH TYPE: PC.
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE PACKAGED 12 PIECES PER BAG IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY D.PARHAM CHECKED BY D.GUITADAURO APPROVED BY D.GALLAGHER	DATE 05/11/2012 05/15/2012 07/13/2012		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY FIBER OPTIC			
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION LC OM1 SMLPX 900um OFNR	SIZE A	FSCM NO. 43321	DWG. NO. FPT9OM1-LC-12PK	REV. A
	SCALE: NONE		CAD FILE: FPT9OM1-LC-12PK.SLDDRW		SHEET 1 OF 1		