

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/20/11	D.GRIFFIN
B	ECN 5696: REMOVED SHARK FIN FROM CONNECTOR	8/31/11	D.FRISIELLO




CHART A					
MODEL NUMBER	LENGTH, M [FT]	COLOR	MODEL NUMBER	LENGTH, M [FT]	COLOR
FPT9OM1-LC-BLK-1	1.0 [3.28]	BLACK	FPT9OM1-LC-AQU-1	1.0 [3.28]	AQUA
FPT9OM1-LC-BLK-2	2.0 [6.56]	BLACK	FPT9OM1-LC-AQU-2	2.0 [6.56]	AQUA
FPT9OM1-LC-BLK-3	3.0 [9.84]	BLACK	FPT9OM1-LC-AQU-3	3.0 [9.84]	AQUA
FPT9OM1-LC-ORG-1	1.0 [3.28]	ORANGE	FPT9OM1-LC-BRN-1	1.0 [3.28]	BROWN
FPT9OM1-LC-ORG-2	2.0 [6.56]	ORANGE	FPT9OM1-LC-BRN-2	2.0 [6.56]	BROWN
FPT9OM1-LC-ORG-3	3.0 [9.84]	ORANGE	FPT9OM1-LC-BRN-3	3.0 [9.84]	BROWN
FPT9OM1-LC-YLW-1	1.0 [3.28]	YELLOW	FPT9OM1-LC-RED-1	1.0 [3.28]	RED
FPT9OM1-LC-YLW-2	2.0 [6.56]	YELLOW	FPT9OM1-LC-RED-2	2.0 [6.56]	RED
FPT9OM1-LC-YLW-3	3.0 [9.84]	YELLOW	FPT9OM1-LC-RED-3	3.0 [9.84]	RED
FPT9OM1-LC-GRY-1	1.0 [3.28]	GRAY	FPT9OM1-LC-WHT-1	1.0 [3.28]	WHITE
FPT9OM1-LC-GRY-2	2.0 [6.56]	GRAY	FPT9OM1-LC-WHT-2	2.0 [6.56]	WHITE
FPT9OM1-LC-GRY-3	3.0 [9.84]	GRAY	FPT9OM1-LC-WHT-3	3.0 [3.84]	WHITE
FPT9OM1-LC-BLU-1	1.0 [3.28]	BLUE	FPT9OM1-LC-VIO-1	1.0 [3.28]	VIOLET
FPT9OM1-LC-BLU-2	2.0 [6.56]	BLUE	FPT9OM1-LC-VIO-2	2.0 [6.56]	VIOLET
FPT9OM1-LC-BLU-3	3.0 [9.84]	BLUE	FPT9OM1-LC-VIO-3	3.0 [3.84]	VIOLET
FPT9OM1-LC-GRN-1	1.0 [3.28]	GREEN	FPT9OM1-LC-ROS-1	1.0 [3.28]	ROSE
FPT9OM1-LC-GRN-2	2.0 [6.56]	GREEN	FPT9OM1-LC-ROS-2	2.0 [6.56]	ROSE
FPT9OM1-LC-GRN-3	3.0 [9.84]	GREEN	FPT9OM1-LC-ROS-3	3.0 [9.84]	ROSE

- NOTES:
1. LC CONNECTOR ASSEMBLY POLISH TYPE: PC.
  2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
  3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	7/7/11		CATEGORY FIBER OPTIC
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D.GUITADAURO	7/7/11	PRODUCT DESCRIPTION LC OM1 SMLPX 900µm OFNR	
PROJECTION 	APPROVED BY D.GALLAGHER	7/7/11	SIZE <b>A</b>	FSCM NO. <b>43321</b>
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		DWG. NO. FPT9OM1-LC	REV. <b>B</b>
	COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: FPT9OM1-LC.SLDDRW
				SHEET 1 OF 1