

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	6/16/14	D.GRIFFIN




CHART A								
FPT9OM2-ST-12PK-1			FPT9OM2-ST-12PK-2			FPT9OM2-ST-12PK-3		
PART NUMBER	LENGTH M [FT]	COLOR	PART NUMBER	LENGTH M [FT]	COLOR	PART NUMBER	LENGTH M [FT]	COLOR
FPT9OM2-ST-BLK-1	1.0 [3.28]	BLACK	FPT9OM2-ST-BLK-2	2.0 [6.56]	BLACK	FPT9OM2-ST-BLK-3	3.0 [9.84]	BLACK
FPT9OM2-ST-ORG-1	1.0 [3.28]	ORANGE	FPT9OM2-ST-ORG-2	2.0 [6.56]	ORANGE	FPT9OM2-ST-ORG-3	3.0 [9.84]	ORANGE
FPT9OM2-ST-YLW -1	1.0 [3.28]	YELLOW	FPT9OM2-ST-YLW -2	2.0 [6.56]	YELLOW	FPT9OM2-ST-YLW -3	3.0 [9.84]	YELLOW
FPT9OM2-ST-GRY-1	1.0 [3.28]	GRAY	FPT9OM2-ST-GRY-2	2.0 [6.56]	GRAY	FPT9OM2-ST-GRY-3	3.0 [9.84]	GRAY
FPT9OM2-ST-BLU-1	1.0 [3.28]	BLUE	FPT9OM2-ST-BLU-2	2.0 [6.56]	BLUE	FPT9OM2-ST-BLU-3	3.0 [9.84]	BLUE
FPT9OM2-ST-GRN-1	1.0 [3.28]	GREEN	FPT9OM2-ST-GRN-2	2.0 [6.56]	GREEN	FPT9OM2-ST-GRN-3	3.0 [9.84]	GREEN
FPT9OM2-ST-AQU-1	1.0 [3.28]	AQUA	FPT9OM2-ST-AQU-2	2.0 [6.56]	AQUA	FPT9OM2-ST-AQU-3	3.0 [9.84]	AQUA
FPT9OM2-ST-BRN-1	1.0 [3.28]	BROW N	FPT9OM2-ST-BRN-2	2.0 [6.56]	BROW N	FPT9OM2-ST-BRN-3	3.0 [9.84]	BROW N
FPT9OM2-ST-RED-1	1.0 [3.28]	RED	FPT9OM2-ST-RED-2	2.0 [6.56]	RED	FPT9OM2-ST-RED-3	3.0 [9.84]	RED
FPT9OM2-ST-W HT-1	1.0 [3.28]	W HITE	FPT9OM2-ST-W HT-2	2.0 [6.56]	W HITE	FPT9OM2-ST-W HT-3	3.0 [9.84]	W HITE
FPT9OM2-ST-VIO-1	1.0 [3.28]	VIOLET	FPT9OM2-ST-VIO-2	2.0 [6.56]	VIOLET	FPT9OM2-ST-VIO-3	3.0 [9.84]	VIOLET
FPT9OM2-ST-ROS-1	1.0 [3.28]	ROSE	FPT9OM2-ST-ROS-2	2.0 [6.56]	ROSE	FPT9OM2-ST-ROS-3	3.0 [9.84]	ROSE

NOTES:

1. ST CONNECTOR ASSEMBLY POLISH TYPE: PC.
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE PACKAGED 12 PIECES PER BAG IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.PARHAM	05/11/2012		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	CHECKED BY D.GUITADAURO	05/15/2012	CATEGORY FIBER OPTICS	
	APPROVED BY D.GALLAGHER	07/13/2012	PRODUCT DESCRIPTION ST OM2 SMLPX 900µm OFNR	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. FPT9OM2-ST-12PK	REV. A
			SCALE: NONE	CAD FILE: FPT9OM2-ST-12PK.SLDDRW
			SHEET 1 OF 1	