

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/17/12	D.GRIFFIN




CHART A								
FPTSNG-ST-12PK-1			FPTSNG-ST-12PK-2			FPTSNG-ST-12PK-3		
PART NUMBER	LENGTH M [FT]	COLOR	PART NUMBER	LENGTH M [FT]	COLOR	PART NUMBER	LENGTH M [FT]	COLOR
FPTSNG-ST-BLK-1	1.0 [3.28]	BLACK	FPTSNG-ST-BLK-2	2.0 [6.56]	BLACK	FPTSNG-ST-BLK-3	3.0 [9.84]	BLACK
FPT9SNG-ST-ORG-1	1.0 [3.28]	ORANGE	FPT9SNG-ST-ORG-2	2.0 [6.56]	ORANGE	FPT9SNG-ST-ORG-3	3.0 [9.84]	ORANGE
FPT9SNG-ST-YLW-1	1.0 [3.28]	YELLOW	FPT9SNG-ST-YLW-2	2.0 [6.56]	YELLOW	FPT9SNG-ST-YLW-3	3.0 [9.84]	YELLOW
FPT9SNG-ST-GRY-1	1.0 [3.28]	GRAY	FPT9SNG-ST-GRY-2	2.0 [6.56]	GRAY	FPT9SNG-ST-GRY-3	3.0 [9.84]	GRAY
FPT9SNG-ST-BLU-1	1.0 [3.28]	BLUE	FPT9SNG-ST-BLU-2	2.0 [6.56]	BLUE	FPT9SNG-ST-BLU-3	3.0 [9.84]	BLUE
FPT9SNG-ST-GRN-1	1.0 [3.28]	GREEN	FPT9SNG-ST-GRN-2	2.0 [6.56]	GREEN	FPT9SNG-ST-GRN-3	3.0 [9.84]	GREEN
FPT9SNG-ST-AQU-1	1.0 [3.28]	AQUA	FPT9SNG-ST-AQU-2	2.0 [6.56]	AQUA	FPT9SNG-ST-AQU-3	3.0 [9.84]	AQUA
FPT9SNG-ST-BRN-1	1.0 [3.28]	BROWN	FPT9SNG-ST-BRN-2	2.0 [6.56]	BROWN	FPT9SNG-ST-BRN-3	3.0 [9.84]	BROWN
FPT9SNG-ST-RED-1	1.0 [3.28]	RED	FPT9SNG-ST-RED-2	2.0 [6.56]	RED	FPT9SNG-ST-RED-3	3.0 [9.84]	RED
FPT9SNG-ST-WHT-1	1.0 [3.28]	WHITE	FPT9SNG-ST-WHT-2	2.0 [6.56]	WHITE	FPT9SNG-ST-WHT-3	3.0 [9.84]	WHITE
FPT9SNG-ST-VIO-1	1.0 [3.28]	VIOLET	FPT9SNG-ST-VIO-2	2.0 [6.56]	VIOLET	FPT9SNG-ST-VIO-3	3.0 [9.84]	VIOLET
FPT9SNG-ST-ROS-1	1.0 [3.28]	ROSE	FPT9SNG-ST-ROS-2	2.0 [6.56]	ROSE	FPT9SNG-ST-ROS-3	3.0 [9.84]	ROSE

NOTES:

1. ST CONNECTOR ASSEMBLY POLISH TYPE: PC.
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE PACKAGED 12 PIECES PER BAG IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.PARHAM	05/11/2012		CHECKED BY D.GUITADAURO
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVED BY D.GALLAGHER	07/13/2012	CATEGORY	FIBER OPTIC
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION	ST SNG SPX 900µm OFNR 12PK
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. FPT9SNG-ST-12PK
		SCALE: NONE	CAD FILE: FPT9SNG-ST-12PK.SLDDRW	SHEET 1 OF 1