



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/26/11	D.GRIFFIN
B	ECN 5755: FLIP LC CONNECTOR SO TAB IS BEHIND PLATE	10/5/11	D.FRISIELLO
C	ECN 5778: UPDATED LC COUPLERS	10/17/11	D.FRISIELLO



- NOTES:
- PANEL MATERIAL: .06 THK COLD ROLLED STEEL.  
FASTENER MATERIAL: THERMOPLASTIC.
  - FINISH: BLACK POWDER COAT.
  - RECOMMENDED MOUNTING HOLE FOR MATING FASTENER  $\phi .252 + .002 / -.000$
  - SUPPLIED WITH DUST CAPS (NOT SHOWN).
  - COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $> 12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $> 60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $> 120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $> 300$ [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	APPROVALS DRAWN BY D. CASTRO CHECKED BY D. PARHAM APPROVED BY M. MARTINEZ	DATE 8/23/11 8/23/11 8/23/11	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY <b>FIBER OPTIC SUB PANELS</b>	
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>FSP-LCD6-CR</b>	REV. <b>C</b>
SCALE: NONE		CAD FILE: FSP-LCD6-CR.SLDDRW		SHEET 1 OF 1	

