



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/14/2020	PHOSPODAR



FANOUT TABLE		
SC	COLOR	MTP
P1	BLUE	1
P2	ORANGE	2
P3	GREEN	3
P4	BROWN	4
P5	GRAY	5
P6	WHITE	6
P7	RED	7
P8	BLACK	8
P9	YELLOW	9
P10	VIOLET	10
P11	PINK	11
P12	AQUA	12



MODEL NO.	DESCRIPTION	FIBER TYPE	SC ADAPTER COLOR
FSP-MTM1-SCD6-M3	MTP Male 12 Fiber to 6 Duplex SC 12 Port MMF OM3	MMF OM3 50/125µm	AQUA

MPO		SC/UPC	
INSERTION LOSS	RETURN LOSS	INSERTION LOSS	RETURN LOSS
≤0.5dB	≥20dB	≤0.30dB	≥25dB

- NOTES:
1. GUARANTEED VALUE ON IL AND RL AS WHOLE MODULE.
 2. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
 3. COUPLERS SHALL BE SHIPPED WITH DUST CAPS INSTALLED. (NOT SHOWN)
 4. COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS DRAWN BY: DZINN CHECKED BY: DFRISIELLO APPROVED BY: PHOSPODAR	DATE 12/14/2020 12/14/2020 12/14/2020		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR		
SCALE: NONE		CAGE CODE: 43321	ITEM NO.: FSP-MTM1-SCD6-M3	REV. A
SHEET 1 OF 1			CAD FILE: FSP-MTM1-SCD6-M3.SLDDRW	