



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	03/30/17	J.LABOY
B	ECN 8743: CHANGE PACKAGING SPEC FROM PKG-00012 TO PS-0031.	05/01/17	J.LABOY
C	ECN 11314 UPDATE PER VENDOR MODEL	08/30/21	DGUTTADAURO



UL20276
 5 TWISTED PAIR INDIVIDUALLY SHIELDED 30AWG
 5 CONDUCTORS 30AWG
 WITH ALUM/POLY FOIL SHIELD AND BRAID SHIELD
 JACKET: PVC, BLACK





NOTES:
 ELECTRICAL CHARACTER:
 1- 100% MAC TO HDTV 2160P TEST
 2- SIGNAL SOURCE RESOLUTION UXGA: 3840*2160P
 3- FREQUENCY: 30Hz

PACKAGING:
 COMPONENT SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPEC PS-0031

ALL DIMENSIONS FOR REFERENCE ONLY

REGULATORY COMPLIANCE:
 EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS B.PUCHASKI	DATE 02/27/17	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	CHECKED BY J.LABOY	DATE 02/27/17	
THIRD-ANGLE PROJECTION 	APPROVED BY B.GATES	DATE 02/27/17	PRODUCT DESCRIPTION HDMI MALE TO DP MALE DONGLE
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321
ITEM NO. HD-DPI-MM-8		SCALE: NONE	CAD FILE: HD-DPI-MM-8.SLDDRW
SHEET 1 OF 1		REV. C	