


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	Initial Release	01/24/11	B.Puchaski

MODEL# HG459U	
SUFFIX	CONNECTOR TYPE
NF	N-FEMALE
NM	N-MALE
RSP	RP SMA-PLUG
RTP	RP TNC-PLUG
RSJ	RP SMA-JACK
RTJ	RP TNC-JACK
RBP	RP BNC PLUG
SM	SMA MALE
TM	TNC MALE
TF	TNC FEMALE



### RoHS Compliant

NOTES:  
 PACKAGING:  
 COMPONENT SHALL BE PACKAGED IN ACCORDANCE  
 WITH L-COM SPEC PKG-00077.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.01 .XXX = ±.005  ANGULAR TOLERANCES: ALL = ± 1°  PROJECTION	APPROVALS DRAWN BY B.Puchaski	DATE 01/24/11		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CHECKED BY T. Vaden	DATE 01/24/11		CATEGORY ANTENNA	
	APPROVED BY T. Vaden	DATE 01/24/11	PRODUCT DESCRIPTION ANT, OMNI 450 to 470MHz 8.5dBi		
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. HG459U
SCALE: NONE		CAD FILE: HG459U.SLDDRW			SHEET 1 OF 1