


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/28/12	D.GRIFFIN



SCREW

#12-24 UNC-2A

WASHER

NOTES:

SCREWS ARE HEAT TREATED FOR STRENGTH AND TO RESIST HEAD STRIPPING.

ALL DIMENSIONS ARE FOR REFERENCE ONLY.

COMPONENTS ARE BULK PACKAGED IN QUANTITIES OF 100 EACH.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY D.FRISIELLO	DATE 8/28/12		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CHECKED BY D.DESJARDIN	DATE 8/28/12		CATEGORY HARDWARE
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION SCREW 10-24x.63 PHP MS W/WASHER	SCALE: NONE   CAD FILE: HP24.SLDDRW   SHEET 1 OF 1	
COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>HP24</b>	REV. <b>A</b>