


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/16/13	D.GRIFFIN



**NOTES:**

- 1- CRIMP SIZES: HEX DIE .068", .213", .256", .324"
  - 2- CABLE TYPE: LMR@@/WBC195, 200, 240, 300, HyperLink CA-195, 200, 240, 400, RG58, RG59, RG62, RG141, RG142, RG6, Belden 8240, 8219
  - 3- COMPONENT SHALL BE PACKAGED AS PER L-COM SPEC PKG-00012
- ALL DIMENSIONS FOR REFERENCE ONLY -

**RoHS Compliant** ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.01 .XXX = ±.005  ANGULAR TOLERANCES: ALL = ± 1°	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY B.PUCHASKI	01/16/13	
	CHECKED BY K.BURGNER	01/16/13	CATEGORY COAXIAL
APPROVED BY P.PESA	01/16/13	PRODUCT DESCRIPTION RATCHET CRIMPING TOOL W/ .068", .213", .256", AND .324" HEX DIE	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b> FSCM NO. <b>43321</b> DWG. NO. <b>HT-CRIMP04</b> REV. <b>A</b>
SCALE: NONE		CAD FILE: HT-CRIMP04.SLDDRW	SHEET 1 OF 1