

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|-----------------|----------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 09/27/12 | D.GRIFFIN |
| | | | |
| | | | |

PRODUCT SPECIFICATIONS

PRODUCT: COAX-SEAL

PACKAGING:

- 60" consumer rolls, 1/2" wide, in retail packaging for pegboard or counter display.
- ▶ **12" industrial rolls, 1/2" wide or 1" wide.** ◀ **4 ROLLS PER BOX**
- Pre-cut strips, 1/2" wide, in 10" and 4" lengths, bulk-packed.
- 10" strip or (2) 4" strips in envelope, with complete instructions for use.

DESCRIPTION:

Easily applied, hand-moldable, tacky black plastic mastic, on peel-away paper backing, suitable for waterproofing a wide variety of connections. Adheres to vinyl and PVC outer jackets. Product is non-conductive, non-contaminating and non-toxic, and UV-stable.

APPLICATIONS:

Provides a long-lasting, waterproof seal for coaxial cable fittings and many other connections. Use for TV and radio antennas, satellite dishes, CATV, wireless networks, marine electronics, feed lines, radar and microwave installations, and many other applications.

VISCOSITY:

ASTM D5-52, gm load, 5 sec.=7.0/10.0 mm. Non-hardening, non-oxidizing at ambient temperature.

TEMPERATURE RANGE:

Apply between 40° F. to 110° F.

PERCENT SOLIDS:

98%

SOLVENTS:

None

OTHER PROPERTIES:

Material is non-staining to paint; stays flexible and maintains a waterproof seal over an extreme range of temperatures. Will not crack at -200° F, will not slump 1 hr. @350° F.

OPTIMUM CURE CYCLE:

Not curable

APPLICATION EQUIPMENT:

Hand applied



12 FOOT ROLL

NOTES:

12 FOOT ROLLS, 1 INCH WIDE, 4 ROLLS PER BOX

RoHS Compliant ✓

| | | | | | |
|---|-------------------------------|---------------------|--|--|------------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.01 .XXX = ±.005 ANGULAR TOLERANCES: ALL = ± 1° | APPROVALS | DATE | | 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 | |
| | DRAWN BY B.PUCHASKI | 09/27/12 | | | |
| | CHECKED BY A.McCHESNEY | 09/27/12 | CATEGORY | COAXIAL | |
| APPROVED BY P.PESA | 09/27/12 | PRODUCT DESCRIPTION | COAX-SEAL SELF-HEALING TAPE 1 INCH WIDE | | |
| PROJECTION | COLOR VARIATIONS MAY OCCUR | SIZE A | FSCM NO. 43321 | DWG. NO. HT-TAPE106 | REV. A |
| | | SCALE: NONE | CAD FILE: HT-TAPE106.SLDDRW | | SHEET 1 OF 1 |