


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVAL
A	INITIAL RELEASE	8/23/12	D.GRIFFIN

NOTES:

1. LENGTH: 8.7 [220] (REF.)
2. FINISH: BLACK OXIDE
3. TOOL IS INDIVIDUALLY PACKAGED



CRIMP RANGE	
.068	[1.73]
.187	[4.75]
.213	[5.41]
.255	[6.48]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] - 60 [1524] = +2 [51] / -0 >60 [1524] - 120 [3048] = +4 [102] / -0 >120 [3048] - 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .2 .XX = .02 .XXX = .005	APPROVALS DRAWN BY D. DESJARDIN	DATE 8/2/12		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	CHECKED BY D. FRISIELLO	DATE 8/22/12		CATEGORY MODULAR		
	APPROVED BY D. PARHAM	DATE 8/22/12	PRODUCT DESCRIPTION HX CRMP TL .068/.187/.213/.255			
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321	DWG. NO. HT230A