


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVAL
A	INITIAL RELEASE	9/28/12	D.FRISIELLO

HT301G RATCHET CRIMPING TOOL



SPECIFICATION:

* Crimping Range :

	.043" 1.09mm				
	.068" 1.73mm	.100" 2.54mm	.137" 3.48mm	.213" 5.41mm	.255" 6.48mm
Description	For Crimping RG 58,59,62,174 Cable Fiber Optic				

* **Length** : 8.7"(220mm)

* **Weight** : 500g

* **Material** :

Frame - Middle Carbon Steel .

Crimper- Made Of Off Wax.

* **Finished** :

Black Oxide Finished With Hardened

* **Replacement die P/N:** HT-3G

NOTES:

COMPONENT SHALL BE PACKAGED PER L-COM SPECIFICATION LSP-010-1.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] - 60 [1524] = +2 [51] / -0 >60 [1524] - 120 [3048] = +4 [102] / -0 >120 [3048] - 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .2 .XX = .02 .XXX = .005	APPROVALS	DATE	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	DRAWN BY D.DESJARDIN	9/28/12				
	CHECKED BY D.FRISIELLO	9/28/12	CATEGORY TOOLS			
	APPROVED BY D.FRISIELLO	9/28/12	PRODUCT DESCRIPTION HEX CRIMP TOOL MULTI USE			
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. HT301G	REV. A
			SCALE: 1:1	CAD FILE: HT301G.SLDDRW	SHEET 1 OF 1	