



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	05/11/2022	GUITADAURO

LEX (LOCAL EXTENDER) MECHANICAL DATA	REX (REMOTE EXTENDER) MECHANICAL DATA
137.3mm x 232.1mm x 33.0mm (5.4"x9.1"x1.3")	137.3mm x 232.1mm x 33.0mm (5.4"x9.1"x1.3")
1x USB 3.1 B RECEPTACLE	4x USB 3.1 "A" RECEPTACLES
1x RJ45 ETHERNET 100/1000 PORT	1x RJ45 ETHERNET 100/1000 PORT
1x RJ45 ETHERNET LINK PORT	1x RJ45 ETHERNET LINK PORT
24V 1A DC LOCKING JACK	24V 2.71A DC LOCKING JACK
920g (2.03 lbs.)	990g (2.18 lbs)
PACKAGE CONTENTS	
1x LEX (LOCAL EXTENDER)	
1x REX (REMOTE EXTENDER)	
1x USB 3.1 GEN 1 CABLE	
2x INTERNATIONAL LOCKING AC ADAPTERS	
2x COUNTRY SPECIFIC POWER CORDS	
1x QUICK START GUIDE	
PACKAGED WEIGHT: 2.91kg (6.42 lbs)	
RANGE	
POINT-TO-POINT:	UP TO 100m OVER CAT 6a/7
USB SUPPORT	
USB SPEEDS:	SUPER SPEED 5 Gbps, HIGH SPEED, FULL SPEED, LOW SPEED
USB BANDWIDTH	UP TO 5 Gbps
DEVICE COMPATIBILITY	ALL DEVICE TYPES AND CLASSES (CONTROL, INTERRUPT, ISOCRONOUS AND BULK)
HOST COMPATIBILITY	OHCI, UHCI, EHCI, kHCI
AVAILABLE CURRENT AT REX	1.2A (6W) PER USB PORT
MAX NUMBER OF USB DEVICES	30
ENVIRONMENTAL	
TEMPERATURE:	0°C-50°C (32°F-122°F) OPERATING, -20°C-70°C (-4°F-158°F) STORAGE
HUMIDITY:	20-80% OPERATING, 10-90% STORAGE (NON-CONDENSING)



**NOTES:**  
1. COMPONENTS SHALL BE PACKAGED TOGETHER IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [5]   ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DFRISIELLO	05/11/2022	
	CHECKED BY ELAMOTT	05/11/2022	
	APPROVED BY GUITADAURO	05/11/2022	
THIRD-ANGLE PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION	NETWORK  ICRON 3104 Raven Pro
	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>   CAGE CODE <b>43321</b>   ITEM NO. <b>ICR3104-PRO</b>	
SCALE: NONE	CAD FILE: ICR3104-PRO.SLDDRW	SHEET 1 OF 1	