

6

5



4

3

2

1

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	08/30/2024	KGLEBOVA	THOUGHTON



DIMENSIONS ARE FOR REFERENCE ONLY.
 DIMENSIONS ARE SHOWN IN MILLIMETERS.

UNLESS OTHERWISE SPECIFIED
 LEADING DIMENSIONS ARE INCHES
 DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

X = ±.5 [5]	FRACTIONS ± 1/32
.XX = ±.02 [0.5]	ANGLES ± 1°
.XXX = ±.005 [0.125]	

CABLE LENGTH TOLERANCES:

≤12 [305]	= ±.125 [-0]
>12 [305] ≤ 60 [1524]	= +.25 [-0]
>60 [1524] ≤ 120 [3048]	= +.4 [102] [-0]
>120 [3048] ≤ 300 [7620]	= +.6 [152] [-0]
>300 [7620]	= +5% [-0]

ALL DIMENSIONS ARE FOR REFERENCE ONLY
 AND SUBJECT TO CHANGE WITHOUT NOTICE
 UN-DIMENSIONED/NON-CRITICAL FEATURES
 MAY VARY IN SIZE AND LOCATION
 COLORS MAY VARY



Website: www.L-com.com
 Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
SCALE NONE	SHEET 1 OF 1

DESCRIPTION
**DISTRIBUTION BOX 8 PORTS WITHOUT ADAPTER AND PIGTAIL
 - INCLUDES SPLICE TRAYS AND ADAPTER PANELS**

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	KGLEBOVA	LCFDB-0208A	A

6

5

4

3

2

1