





6 5 4 3 2 1


REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	08/30/2024	KGLEBOVA	THOUGHTON

F  
E  
D  
C  
B  
A

F  
E  
D  
C  
B  
A



NUMBER	COLOR
1	BLUE
2	ORANGE
3	GREEN
4	BROWN
5	GREY
6	WHITE
7	RED
8	BLACK



DIMENSIONS ARE FOR REFERENCE ONLY.  
DIMENSIONS ARE SHOWN IN MILLIMETERS.

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS

TOLERANCES:

X = ±.5 [5]	FRACTIONS ± 1/32
.XX = ±.02 [0.5]	ANGLES ± 1°
.XXX = ±.005 [0.125]	

CABLE LENGTH TOLERANCES:

≤12 [305]	= ±.125 [-0]
>12 [305] ≤ 60 [1524]	= +.2 [-.1] / -0
>60 [1524] ≤ 120 [3048]	= +.4 [10.2] / -0
>120 [3048] ≤ 300 [7620]	= +.6 [15.2] / -0
>300 [7620]	= +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE  
UN-DIMENSIONED/NON-CRITICAL FEATURES  
MAY VARY IN SIZE AND LOCATION  
COLORS MAY VARY

**L-com**  
an INFINITE brand

Website: [www.L-com.com](http://www.L-com.com)  
Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

SCALE	SHEET
NONE	1 OF 1

DESCRIPTION  
**DISTRIBUTION BOX 8 PORTS WITH 8X SC SM SIMPLEX ADAPTER AND 1:8 SC PLC SPLITTER**

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	KGLEBOVA	LCFDB-108B-P8SC	A

6 5 4 3 2 1