





6 5 4 3 2 1

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	08/30/2024	KGLEBOVA	THOUGHTON





F  
E  
D  
C  
B  
A

F  
E  
D  
C  
B  
A



NUMBER	COLOR	NUMBER	COLOR
1	BLUE	9	BLUE
2	ORANGE	10	ORANGE
3	GREEN	11	GREEN
4	BROWN	12	BROWN
5	GREY	13	GREY
6	WHITE	14	WHITE
7	RED	15	RED
8	BLACK	16	BLACK



DIMENSIONS ARE FOR REFERENCE ONLY.  
DIMENSIONS ARE SHOWN IN MILLIMETERS.

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS

TOLERANCES:  
X = ±.5 [5] FRACTIONS ± 1/32  
.XX = ±.02 [0.5] ANGLES ± 1°  
.XXX = ±.005 [0.125]

CABLE LENGTH TOLERANCES:  
≤12 [305] = ±.25 [6.35] / -0  
>12 [305] ≤ 60 [1524] = +.2 [5.08] / -0  
>60 [1524] ≤ 120 [3048] = +.4 [10.16] / -0  
>120 [3048] ≤ 300 [7620] = +.6 [15.24] / -0  
>300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE  
UN-DIMENSIONED/NON-CRITICAL FEATURES  
MAY VARY IN SIZE AND LOCATION  
COLORS MAY VARY

**L-com**  
an INFINITE® brand  
Website: www.L-com.com  
Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND  
TOLERANCES PER ASME Y14.5

SCALE NONE SHEET 1 OF 1

DESCRIPTION  
DISTRIBUTION BOX 16 PORTS WITH 16X SC/APC SM DX  
ADAPTER AND 1:16 SC/APC PLC SPLITTER CASSETTE

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	KGLEBOVA	LCFDB-216A-P16SCA	A

6 5 4 3 2 1