



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	06/21/2023	HBAKKE	GUTTADAURO



**PIN ASSIGNMENTS:**




**NOTES:**

- CABLE: (7/0.08T\*1P+1C+AL+MY)\*5C+7/0.08T\*5C+ADB  
OD: 5.5mm, BLACK NYLON BRAID, JACKET: BLACK TPE (LSZH)
- ELECTRICAL TEST:
  - 100% OPEN SHORT & MISS WIRE TEST
  - CONTACT RESISTANCE: 5 OHM MAX
  - INSULATION RESISTANCE: 10M OHM MIN
  - HI-POT TEST: DC 300V/10ms
- CABLE SHALL BE TESTED FOR CONTINUITY.
- CABLE SHALL BE INDIVIDUALLY PACKAGED.

PART NUMBER	LENGTH	
	FEET	METERS
LDPMDP-LSZH4KMM-1M	3.28	1.0
LDPMDP-LSZH4KMM-3M	9.84	3.0

**REGULATORY COMPLIANCE:**

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0  ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [.5]   ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	DRAWN BY HBAKKE	06/21/2023		CATEGORY  <b>AUDIO/VIDEO</b>	
	CHECKED BY DMAY	06/21/2023			
	APPROVED BY RCARLESCO	06/21/2023			
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY  COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION <b>DP to MDP, M/M, LSZH, Alum Shell, 4K @ 60 Hz, Black Nylon Braid</b>	SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. <b>LDPMDP-LSZH4KMM</b>	REV. <b>A</b>
THIRD-ANGLE PROJECTION 	SCALE: NONE	CAD FILE: LDPMDP-LSZH4KMM.SLDDRW	SHEET 1 OF 1		