


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	06/21/2023	HBAKKE	GUTTADAURO



PIN ASSIGNMENTS:

P1	P2
PIN 3	PIN 1
PIN 5	PIN 3
PIN 1	PIN 5
PIN 2	PIN 18
PIN 4	PIN 13
PIN 6	PIN 14
PIN 9	PIN 4
PIN 11	PIN 6
PIN 7	PIN 2
PIN 10	PIN 10
PIN 12	PIN 12
PIN 8	PIN 8
PIN 15	PIN 7
PIN 17	PIN 9
PIN 13	PIN 11
PIN 16	PIN 15
PIN 18	PIN 17
PIN 14	PIN 16
PIN 19	PIN 19
PIN 20	PIN 20
SHELL	SHELL


NOTES:

- CABLE: (7/0.08T*1P+1C+AL+MY)*5C+7/0.08T*5C+ADB
OD: 5.5mm, BLACK NYLON BRAID, JACKET: BLACK TPE (LSZH)
- ELECTRICAL TEST:
 - 100% OPEN SHORT & MISS WIRE TEST
 - CONTACT RESISTANCE: 5 OHM MAX
 - INSULATION RESISTANCE: 10M OHM MIN
 - HI-POT TEST: DC 300V/10ms
- CABLE SHALL BE TESTED FOR CONTINUITY.
- CABLE SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

PART NUMBER	LENGTH	
	FEET	METERS
LDPMDP-LSZH4KMM-1M	3.28	1.0
LDPMDP-LSZH4KMM-3M	9.84	3.0

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		L-com™ an INFINIT® brand 50 High Street, West Mill, North Andover, MA 01845 USA Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY HBAKKE		06/21/2023			
		CHECKED BY DMAY		06/21/2023			
		APPROVED BY RCARLESCO		06/21/2023			
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] .XX = ± .02 [.5] .XXX = ± .005 [.13]		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY		AUDIO/VIDEO	
				PRODUCT DESCRIPTION			
				DP to MDP, M/M, LSZH, Alum Shell, 4K @ 60 Hz, Black Nylon Braid			
THIRD-ANGLE PROJECTION		COLOR VARIATIONS MAY OCCUR		SIZE A	CAGE CODE 43321	ITEM NO. LDPMDP-LSZH4KMM	REV. A
				SCALE: NONE		CAD FILE: LDPMDP-LSZH4KMM.SLDDRW	SHEET 1 OF 1