

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	03/21/2023	DMAY	DGUTTADAURO

D

C


B

A



P1
HDMI AM PIN: G/F,
SHELL: GOLD PLATED

PIN Assignment
P1 HDMI AM P2 DVI 24+1 M



P2
DVI24+1 M PIN: G/F,
SHELL: GOLD PLATED

PART NUMBER	LENGTH	
	FEET	METERS
LHDDVI-AMM-3FT	3.00	.915 ±.03
LHDDVI-AMM-10FT	10.00	3.05 ±.03

- NOTES:
- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL, APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
 - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
 - DIMENSIONS FOR REFERENCE ONLY.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [1.3]	APPROVALS DRAWN BY DMAY CHECKED BY HBAKKE APPROVED BY DGUTTADAURO	DATE 03/21/2023 03/21/2023 03/21/2023	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY AUDIO/VIDEO	
	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION HDMI 2.0 TO DVI, M/M, BLUE ALUMINUM SHELL WITH BLACK NYLON BRAID CABLE, 1080P @60Hz	ITEM NO. LHDDVI-AMM
	THIRD-ANGLE PROJECTION 	SCALE: NONE	CAGE CODE 43321	REV. A

SCALE: NONE CAD FILE: LHDDVI-AMM.SLDDRW SHEET 1 OF 1