



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	03/21/2023	DMAY	DGUTTADAURO



**P1**  
HDMI AM PIN: G/F,  
SHELL: GOLD PLATED

**PIN Assignment**  
P1 HDMI AM    P2 DVI 24+1 M



PART NUMBER	LENGTH	
	FEET	METERS
LHDDVI-ZMM-3FT	3.00	.915 ±.03
LHDDVI-ZMM-10FT	10.00	3.05 ±.03

- NOTES:
- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL, APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
  - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
  - DIMENSIONS FOR REFERENCE ONLY.

REGULATORY COMPLIANCE:  
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5]    FRACTIONS ± 1/32 .XX = ±.02 [5]    ANGLES ± 1° .XXX = ±.005 [13]	APPROVALS	DATE	 an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DMAY	03/21/2023	
THIRD-ANGLE PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION HDMI 2.0 TO DVI, M/M, LIGHT GUN ZINC ALLOY SHELL WITH BLACK NYLON BRAID CABLE, 1080P @60Hz	ITEM NO. LHDDVI-ZMM
	COLOR VARIATIONS MAY OCCUR	SCALE: NONE	SHEET 1 OF 1 CAD FILE: LHDDVI-ZMM.SLDDRW