


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	06/20/2023	HBAKKE	GUTTADAURO



P1
MINI DISPLAYPORT MALE CONNECTOR
WITH GOLD PLATED CONTACTS

P2
HDMI MALE CONNECTOR
WITH PCBA & GOLD PLATED CONTACTS

Pin Assignments:



NOTES:

- CABLE: (7/0.08T*1P+1C+AL+MY)*5C+7/0.08T*5C+ADB
OD: 5.5mm, BLACK NYLON BRAID, JACKET: PVC, BLACK
- ELECTRICAL TEST:
 - 100% OPEN SHORT & MISS WIRE TEST
 - CONTACT RESISTANCE: 5 OHM MAX
 - INSULATION RESISTANCE: 10M OHM MIN
 - HI-POT TEST: DC 300V/10ms
- CABLE SHALL BE TESTED FOR CONTINUITY.
- CABLE SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

PART NUMBER	LENGTH	
	FEET	METERS
LMDPHDMI4K-MM-1M	3.28	1.0
LMDPHDMI4K-MM-3M	9.84	3.0

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13] THIRD-ANGLE PROJECTION 	APPROVALS	DATE	 an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY HBAKKE	06/20/2023	
	CHECKED BY DMAY	06/20/2023	
	APPROVED BY RCARLESCO	06/20/2023	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CATEGORY AUDIO/VIDEO		PRODUCT DESCRIPTION MDP to HDMI, M/M, Alum Shell, 4K @ 60 Hz, Black Nylon Braid
COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	
	ITEM NO. LMDPHDMI4K-MM	REV. A	
	SCALE: NONE	CAD FILE: LMDPHDMI4K-MM.SLDDRW	