

6

5

4

3

2


1

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	2/1/2024	DMAY	DGUTTADAURO


F

F


LENGTH

**P1**

USB 3.0 TYPE C MALE
CONNECTOR
W/ GOLD PLATED CONTACTS



CABLE: USB3.0 [1P*32#(7/0.08TC ID:0.58 FMPE)+AL+HM]
*2C+1P*32#(7/0.08TC ID:0.45mm HDPE)+4C*32#(7/0.08TC ID: 0.45 HDPE)
+2C*28#(7/0.127TC ID: 0.9mm HDPE)+AL+S(56/0.08TC)
JACKET: BLACK PVC OD:4.8mm+ BLACK NYLON BRAID OD:5.1±0.2mm

**P2**

HDMI TYPE A MALE
CONNECTOR
W/ GOLD PLATED CONTACTS


D

D

C

C

PART NUMBER	LENGTH	
	FEET	METERS
LUSBCHDMI4K-MM-1M	3.28	1.0±.03
LUSBCHDMI4K-MM-3M	9.84	3.0±.03

**NOTES:**

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

B

B

A

A

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS


TOLERANCES:
X = ±.2 [5] | FRACTIONS ± 1/32
.XX = ±.02 [0.5] | ANGLES ± 1°
.XXX = ±.005 [0.13]

CABLE LENGTH TOLERANCES:
≤12 [305] = +1 [25] / -0
>12 [305] ≤ 60 [1524] = +2 [51] / -0
>60 [1524] ≤ 120 [3048] = +4 [102] / -0
>120 [3048] ≤ 300 [7620] = +6 [152] / -0
>300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE.
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY

L-com
an INFINIT@ brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE	SHEET
NONE	1 OF 1

DESCRIPTION

USB C TO HDMI M/M 4K@60Hz

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	DMAY	LUSBCHDMI4K-MM	A

6

5

4

3

2

1