


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISION |     |                 |            |            |            |
|----------|-----|-----------------|------------|------------|------------|
| ZONE     | REV | DESCRIPTION     | DATE       | CHANGED BY | APPROVED   |
|          | A   | INITIAL RELEASE | 06/20/2023 | HBAKKE     | GUTTADAURO |



**P1**  
USB 3.1 TYPE C MALE  
5 AMP CONNECTOR  
WITH GOLD PLATED CONTACTS


**P2**  
MINI DISPLAYPORT MALE CONNECTOR  
WITH PCBA & GOLD PLATED CONTACTS

**NOTES:**

- CABLE: (7/0.08T\*1P+1C+AL+MY)\*5C+7/0.08T\*5C+ADB  
OD: 5.5mm, BLACK NYLON BRAID, JACKET: PVC, BLACK
- ELECTRICAL TEST:
  - 100% OPEN SHORT & MISS WIRE TEST
  - CONTACT RESISTANCE: 5 OHM MAX
  - INSULATION RESISTANCE: 10M OHM MIN
  - HI-POT TEST: DC 300V/10ms
- CABLE SHALL BE TESTED FOR CONTINUITY.
- CABLE SHALL BE INDIVIDUALLY PACKAGED.

| PART NUMBER      | LENGTH |        |
|------------------|--------|--------|
|                  | FEET   | METERS |
| LUSBCMDP4K-MM-1M | 3.28   | 1.0    |
| LUSBCMDP4K-MM-3M | 9.84   | 3.0    |

**Pin Assignments:**



**REGULATORY COMPLIANCE:**

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

|                                                                                                                                                                                                                                                                                                                                                                                                                            |                                                                                                     |                                                |                                                                                                                                             |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------|------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------|
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONS ARE IN INCHES [mm]<br><br>OVERALL CABLE LENGTH TOLERANCE:<br>≤12 [305] = +1 [25] / -0<br>>12 [305] ≤60 [1524] = +2 [51] / -0<br>>60 [1524] ≤120 [3048] = +4 [102] / -0<br>>120 [3048] ≤300 [7620] = +6 [152] / -0<br>>300 [7620] = +5% / -0<br><br>ALL OTHER DIMENSIONAL TOLERANCES:<br>.X = ± .2 [5]   FRACTIONS ± 1/32<br>.XX = ± .02 [5]   ANGLES ± 1°<br>.XXX = ± .005 [1.3] | APPROVALS<br>DRAWN BY: HBAKKE<br>CHECKED BY: DMAY<br>APPROVED BY: RCARLESCO                         | DATE<br>06/20/2023<br>06/20/2023<br>06/20/2023 | <b>L-com</b><br>an INFINITI® brand<br>50 High Street, West Mill,<br>North Andover, MA 01845 USA.<br>Phone: 1.800.341.5266<br>1.978.682.6936 |
|                                                                                                                                                                                                                                                                                                                                                                                                                            | CONFIGURATION DETAILS OF<br>UNDIMENSIONED FEATURES<br>MAY VARY<br><br>COLOR VARIATIONS<br>MAY OCCUR | CATEGORY<br><b>AUDIO/VIDEO</b>                 | PRODUCT DESCRIPTION<br><b>USBC to MDP, M/M, Alum Shell, 4K @ 60 Hz,<br/>Black Nylon Braid</b>                                               |
| THIRD-ANGLE PROJECTION<br>                                                                                                                                                                                                                                                                                                                                                                                                 | SIZE<br><b>A</b>                                                                                    | CAGE CODE<br><b>43321</b>                      | ITEM NO.<br><b>LUSBCMDP4K-MM</b>                                                                                                            |