


REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	03/21/2023	DMAY	DGUTTADAURO



PART NUMBER	LENGTH	
	FEET	METERS
LUSBDP-MM-05M	1.64	0.5 ± .03
LUSBDP-MM-1M	3.28	1.0 ± .03
LUSBDP-MM-2M	6.56	2.0 ± .03
LUSBDP-MM-3M	9.84	3.0 ± .03

- NOTES:
1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL, APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
 2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
 4. DIMENSIONS FOR REFERENCE ONLY.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE				50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +5% / -0		DRAWN BY DMAV		03/21/2023		CATEGORY		AUDIO/VIDEO	
ALL OTHER DIMENSIONAL TOLERANCES: $.X = \pm .2$ [5] FRACTIONS $.XX = \pm .02$ [15] $\pm 1/32$ $.XXX = \pm .005$ [13] ANGLES $\pm 1^\circ$		CHECKED BY HBAKKE		03/21/2023		PRODUCT DESCRIPTION		USB C TO DISPLAYPORT, SILVER ALUMINUM SHELL WITH BLACK NYLON BRAIDED CABLE, 8K @60Hz	
THIRD-ANGLE PROJECTION 		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		APPROVED BY DGUTTADAURO		SIZE A		CAGE CODE 43321	
		COLOR VARIATIONS MAY OCCUR				ITEM NO. LUSBDP-MM		REV. A	
				SCALE: NONE		CAD FILE: LUSBDP-MM.SLDDRW		SHEET 1 OF 1	