



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/25/10	D.GRIFFIN
B	ECN4691: ADDED M12 CONNECTOR CALL-OUT	04/16/10	DFP
C	ECN 6206: ADDED "D-CODED" FOR CLARIFICATION, REVISED WIRE MAP	6/1/12	D.FRISIELLO



WIRING MAP			
PAIR	"P1"	COLOR	"J1"
1	1	WHITE/ORANGE	1
	3	ORANGE	3
2	2	WHITE/GREEN	2
	4	GREEN	4

PART NUMBER	LENGTH	
	FEET	METERS
M12M12F4D-0.5	1.64	0.5
M12M12F4D-1	3.28	1
M12M12F4D-2	6.56	2
M12M12F4D-3	9.84	3
M12M12F4D-5	16.41	5

- NOTE:
1. WATERPROOF RATING: IP68.
 2. MOLDED HOOD: POLYURETHANE, BLACK.
 3. SCREW NUT: ZINC ALLOY, NICKEL PLATED.
 4. PINS: COPPER ALLOY, GOLD PLATED.
 5. CABLE ASSEMBLIES INDIVIDUALLY PACKAGED IN A POLY BAG PER L-COM SPECIFICATION PS-0031.
 6. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
 7. CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. PARHAM CHECKED BY D. CASTRO APPROVED BY P. McNEIL	01/21/2010	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY TELECOM/MODULAR
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321 DWG. NO. M12M12F4D PRODUCT DESCRIPTION CA M12 TO M12 F 4 POS D
		SCALE: NONE	CAD FILE: M12M12F4D.SLDDRW SHEET 1 OF 1