


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES MCSC-SC-01-OD1	10/20/14	D.FRISIELLO



MODEL NUMBER	LENGTH	
	METERS	FEET
MCSC-SC-01	1.0	3.28
MCSC-SC-02	2.0	6.56
MCSC-SC-03	3.0	9.84
MCSC-SC-04	4.0	13.12
MCSC-SC-05	5.0	16.41

NOTES:

1. SC CONNECTOR ASSEMBLY POLISH TYPE: PC.
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY MCCORMICK	04/08/02		
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	APPROVED BY R.CARRICK	04/08/02	CATEGORY FIBER OPTICS
	COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION DUAL SC-SC MODE CNDITIONING		SIZE A
SCALE: NONE		FSCM NO. 43321	DWG. NO. MCSC-SC	REV. A
CAD FILE: MCSC-SC.SLDDRW			SHEET 1 OF 1	