



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/2/15	D.GRIFFIN
B	ECN 9020; REVISE NOTES TO REMOVE HDMI LABEL	12/22/2017	B.ZHANG






HDMI TYPE A MALE CONNECTOR
GOLD PLATED CONTACTS



UL STYLE 20276,
(5) INDIVIDUALLY SHIELDED TWISTED PAIRS, 32AWG, WITH DRAIN WIRE,
(4) INDIVIDUAL CONDUCTORS, 32AWG,
OVERALL SHIELD: ALUMINUM MYLAR WITH DRAIN WIRE PLUS
BRAIDED TINNED COPPER
OUTER JACKET: PVC, BLACK



HDMI TYPE D MALE CONNECTOR
GOLD PLATED CONTACTS



PART NO.	LENGTH
	METERS [FEET]
MICHD-HD-0.5	0.5 [1.64]
MICHD-HD-1	1.0 [3.28]
MICHD-HD-2	2.0 [6.56]
MICHD-HD-3	3.0 [9.84]

NOTES

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
3. THE DRAIN WIRES OF TMDS MAY OR MAY NOT BE SHORTED.

REGULATORY COMPLIANCE:
CE2011/65/EU (ROHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [.51] .XXX = ±.005 [.13]	APPROVALS	DATE
	DRAWN BY S.LI	07/27/2015
	CHECKED BY B.ZHANG	07/27/2015
	APPROVED BY S.PAN	07/27/2015
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	
	COLOR VARIATIONS MAY OCCUR	

L-com Global Connectivity 50 HIGH STREET NORTH ANDOVER, MA 01845

CATEGORY: VIDEO

PRODUCT DESCRIPTION: CA, MICRO HDMI M/HDMI M

SIZE: A	FSCM NO.: 43321	DWG. NO.: MICHD-HD	REV.: B
SCALE: NONE		CAD FILE: MICHD-HD.SLDDRW	SHEET 1 OF 1