


WIRING MAP					
J1	J2	J3	COLOR	J4	J5
12			BLUE	1	
11			ORANGE	2	
10			GREEN	3	
9			BROWN	4	
	12		GRAY	5	
	11		WHITE	6	
	10		RED	7	
	9		BLACK	8	
		9	YELLOW	9	
		10	PURPLE	10	
		11	ROSE	11	
		12	AQUA	12	
4			BLUE/BLACK	1	
3			ORANGE/BLACK	2	
2			GREEN/BLACK	3	
1			BROWN/BLACK	4	
	4		GRAY/BLACK	5	
	3		WHITE/BLACK	6	
	2		RED/BLACK	7	
	1		BLACK / WHITE	8	
		4	YELLOW/BLACK	9	
		3	PURPLE/BLACK	10	
		2	ROSE/BLACK	11	
		1	AQUA/BLACK	12	

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	03/28/2019	PHOSPODAR



PART NUMBER	LENGTH METERS (FEET)	BREAKOUT METERS (FEET)
MPF308-MPF212OM4Z-1	1.0 (3.28)	0.3 (1.00)
MPF308-MPF212OM4Z-3	3.0 (9.84)	0.6 (2.00)
MPF308-MPF212OM4Z-5	5.0 (16.40)	0.6 (2.00)
MPF308-MPF212OM4Z-10	10.0 (32.81)	0.6 (2.00)

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS TOLERANCES: .X±.2 [5.08] FRACTIONS ± 1/32 .XX±.01 [.25] ANGLES ± 1° .XXX±.005 [.13]		 an INFINITO brand 50 High Street, West Mill, 3rd Floor, Suite #30 North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 Fax: 1.978.689.9484 e-mail: CustomerService@L-com.com		THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF L-COM GLOBAL CONNECTIVITY. ALL RIGHTS RESERVED.	
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. THIRD-ANGLE PROJECTION		www.L-com.com		SHEET 1 OF 1 SCALE N/A	
SIZE	CAGE	DRAWN BY	PART NUMBER	REV	
A	43321	DZINN	MPF308-MPF212OM4Z	A	