


| REVISIONS | | | |
|-----------|------------------------|------------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | REV A DRAWING RELEASED | 03/27/2019 | PHOSPODAR |



| WIRING MAP | |
|-------------|----------|
| MPO FIBER # | LC COLOR |
| 1 | BLUE |
| 2 | ORANGE |
| 3 | GREEN |
| 4 | BROWN |
| 5 | GRAY |
| 6 | WHITE |
| 7 | RED |
| 8 | BLACK |
| 9 | YELLOW |
| 10 | PURPLE |
| 11 | ROSE |
| 12 | AQUA |

| PART NUMBER | FIBER MODE | LENGTH METERS [FEET] | BREAKOUT METERS [FEET] |
|------------------|----------------------|----------------------|------------------------|
| MPM12OM5-FLCZ-05 | 50/125 MULTIMODE OM5 | 0.5 [1.64] | .30 [1.0] |
| MPM12OM5-FLCZ-1 | 50/125 MULTIMODE OM5 | 1.0 [3.28] | .61 [2.0] |
| MPM12OM5-FLCZ-3 | 50/125 MULTIMODE OM5 | 3.0 [9.84] | .61 [2.0] |
| MPM12OM5-FLCZ-5 | 50/125 MULTIMODE OM5 | 5.0 [16.40] | .61 [2.0] |
| MPM12OM5-FLCZ-10 | 50/125 MULTIMODE OM5 | 10.0 [32.81] | .61 [2.0] |

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

| | |
|-----------------|-------------|
| X±.2 [5.08] | FRACTIONS |
| .XX±.01 [.25] | ± 1/32 |
| .XXX±.005 [.13] | ANGLES ± 1° |

ALL DIMENSIONS SHOWN
ARE FOR REFERENCE ONLY.

THIRD-ANGLE PROJECTION

L-com
an INFINITO brand
50 High Street, West Mill, 3rd Floor, Suite #30
North Andover, MA 01845 USA.
Phone: 1.800.341.5266 | 1.978.682.6936
Fax: 1.978.689.9484
www.L-com.com | e-mail: CustomerService@L-com.com

| | | | | |
|------|-------|------------|---------------|-----|
| SIZE | CAGE | DRAWN BY | PART NUMBER | REV |
| A | 43321 | DFRISIELLO | MPM12OM5-FLCZ | A |

THE INFORMATION AND
DESIGN IN THIS DOCUMENT
IS THE PROPERTY OF
L-COM GLOBAL CONNECTIVITY.
ALL RIGHTS RESERVED.

SHEET 1 OF 1

SCALE N/A

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.