


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	03/27/2019	PHOSPODAR



WIRING MAP	
MPO FIBER #	SC COLOR
1	BLUE
2	ORANGE
3	GREEN
4	BROWN
5	GRAY
6	WHITE
7	RED
8	BLACK
9	YELLOW
10	PURPLE
11	ROSE
12	AQUA

PART NUMBER	FIBER MODE	LENGTH METERS [FEET]	BREAKOUT METERS [FEET]
MPM12OM5-SCZ-05	50/125 MULTIMODE OM5	0.5 [1.64]	.30 [1.0]
MPM12OM5-SCZ-1	50/125 MULTIMODE OM5	1.0 [3.28]	.61 [2.0]
MPM12OM5-SCZ-3	50/125 MULTIMODE OM5	3.0 [9.84]	.61 [2.0]
MPM12OM5-SCZ-5	50/125 MULTIMODE OM5	5.0 [16.40]	.61 [2.0]
MPM12OM5-SCZ-10	50/125 MULTIMODE OM5	10.0 [32.81]	.61 [2.0]

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS

**TOLERANCES:**

X=± .2 [5.08]	FRACTIONS
.XX=± .01 [ .25]	± 1/32
.XXX=± .005 [ .13]	ANGLES ± 1°

ALL DIMENSIONS SHOWN  
ARE FOR REFERENCE ONLY.

THIRD-ANGLE PROJECTION

an INFINITO brand  
50 High Street, West Mill, 3rd Floor, Suite #30  
North Andover, MA 01845 USA.  
Phone: 1.800.341.5266 | 1.978.682.6936  
Fax: 1.978.689.9484  
www.L-com.com | e-mail: CustomerService@L-com.com

SIZE	CAGE	DRAWN BY	PART NUMBER	REV
A	43321	DFRISIELLO	MPM12OM5-SCZ	A

THE INFORMATION AND  
DESIGN IN THIS DOCUMENT  
IS THE PROPERTY OF  
L-COM GLOBAL CONNECTIVITY.  
ALL RIGHTS RESERVED.

SHEET 1 OF 1

SCALE N/A

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.