


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
B	ECN 10052, REMOVED "BLACK" FROM 13-19, 21-24, "/WHITE" FROM 20	08/21/2019	PHOSPODAR



WIRING MAP	
MPO FIBER #	ST COLOR
1	BLUE
2	ORANGE
3	GREEN
4	BROWN
5	GRAY
6	WHITE
7	RED
8	BLACK
9	YELLOW
10	PURPLE
11	ROSE
12	AQUA
13	BLUE
14	ORANGE
15	GREEN
16	BROWN
17	GRAY
18	WHITE
19	RED
20	BLACK
21	YELLOW
22	PURPLE
23	ROSE
24	AQUA

PART NUMBER	FIBER MODE	LENGTH METERS [FEET]	BREAKOUT METERS [FEET]
MPM24OM4-STR-05	50/125 MULTIMODE OM4	0.5 [1.64]	.30 [1.0]
MPM24OM4-STR-1	50/125 MULTIMODE OM4	1.0 [3.28]	.61 [2.0]
MPM24OM4-STR-3	50/125 MULTIMODE OM4	3.0 [9.84]	.61 [2.0]
MPM24OM4-STR-5	50/125 MULTIMODE OM4	5.0 [16.40]	.61 [2.0]
MPM24OM4-STR-10	50/125 MULTIMODE OM4	10.0 [32.81]	.61 [2.0]

△ B

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS

**TOLERANCES:**

X±.2 [5.08]	FRACTIONS
.XX±.01 [.25]	± 1/32
.XXX±.005 [.13]	ANGLES ± 1°

ALL DIMENSIONS SHOWN  
ARE FOR REFERENCE ONLY.

THIRD-ANGLE PROJECTION

an INFINITI brand  
50 High Street, West Mill, 3rd Floor, Suite #30  
North Andover, MA 01845 USA.  
Phone: 1.800.341.5266 | 1.978.682.6936  
Fax: 1.978.689.9484  
www.L-com.com | e-mail: CustomerService@L-com.com

SIZE	CAGE	DRAWN BY	PART NUMBER	REV
A	43321	DFRISIELLO	MPM24OM4-STR	B

THE INFORMATION AND  
DESIGN IN THIS DOCUMENT  
IS THE PROPERTY OF  
L-COM GLOBAL CONNECTIVITY.  
ALL RIGHTS RESERVED.

SHEET 1 OF 1

SCALE N/A

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.