



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/25/13	D.GRIFFIN
B	ECN 7107: ADDED JACKET TYPE TO CHART. REMOVED ALL OM4 P/NS. UPD ROHS	10/17/13	D.FRISIELLO



MULTIMODE WIRING MAP (8 MPO CONNECTOR)	
MPO FIBER #	LC COLOR
N/C	N/C
2	BLUE
3	ORANGE
4	GREEN
5	BROWN
6	GRAY
7	WHITE
N/C	N/C

SINGLE MODE WIRING MAP (12 MPO CONNECTOR)	
MPO FIBER #	LC COLOR
N/C	N/C
N/C	N/C
N/C	N/C
4	BLUE
5	ORANGE
6	GREEN
7	BROWN
8	GRAY
9	WHITE
N/C	N/C
N/C	N/C
N/C	N/C

NOTES:

- SEE SHEET 2 FOR PART NUMBERS, FIBER MODES, JACKET TYPES, COLORS, AND LENGTHS.
- MPO CONNECTOR MULTIMODE ASSEMBLY POLISH TYPE: UPC.
MPO CONNECTOR SINGLE MODE ASSEMBLY POLISH TYPE: APC.
LC CONNECTOR ASSEMBLY POLISH TYPE: PC.
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	7/19/13		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [1.27]	CHECKED BY D.DESJARDIN	7/19/13	CATEGORY FIBER OPTICS	
	APPROVED BY D.GALLAGHER	7/19/13	PRODUCT DESCRIPTION 6 RIB MPO-M/ FLC	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. MPM6S-FLC	REV. B
			SCALE: NONE	CAD FILE: MPM6S-FLC.SLDRW
				SHEET 1 OF 2

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



PART NUMBER	FIBER MODE	JACKET TYPE	COLOR	METERS [FEET]
MPM6OM1-FLC-05	62.5/125 MULTIMODE OM1	OFNR (RISER) RATED	ORANGE	0.5 [1.64]
MPM6OM1-FLC-1	62.5/125 MULTIMODE OM1	OFNR (RISER) RATED	ORANGE	1.0 [3.28]
MPM6OM1-FLC-5	62.5/125 MULTIMODE OM1	OFNR (RISER) RATED	ORANGE	5.0 [16.40]
MPM6OM1-FLC-10	62.5/125 MULTIMODE OM1	OFNR (RISER) RATED	ORANGE	10.0 [32.81]
MPM6OM2-FLC-05	50/125 MULTIMODE OM2	OFNR (RISER) RATED	ORANGE	0.5 [1.64]
MPM6OM2-FLC-1	50/125 MULTIMODE OM2	OFNR (RISER) RATED	ORANGE	1.0 [3.28]
MPM6OM2-FLC-5	50/125 MULTIMODE OM2	OFNR (RISER) RATED	ORANGE	5.0 [16.40]
MPM6OM2-FLC-10	50/125 MULTIMODE OM2	OFNR (RISER) RATED	ORANGE	10.0 [32.81]
MPM6OM3-FLC-05	50/125 MULTIMODE OM3	OFNR (RISER) RATED	AQUA	0.5 [1.64]
MPM6OM3-FLC-1	50/125 MULTIMODE OM3	OFNR (RISER) RATED	AQUA	1.0 [3.28]
MPM6OM3-FLC-5	50/125 MULTIMODE OM3	OFNR (RISER) RATED	AQUA	5.0 [16.40]
MPM6OM3-FLC-10	50/125 MULTIMODE OM3	OFNR (RISER) RATED	AQUA	10.0 [32.81]
MPM6S-FLC-05	9/125 SINGLE MODE OS1	OFNR (RISER) RATED	YELLOW	0.5 [1.64]
MPM6S-FLC-1	9/125 SINGLE MODE OS1	OFNR (RISER) RATED	YELLOW	1.0 [3.28]
MPM6S-FLC-5	9/125 SINGLE MODE OS1	OFNR (RISER) RATED	YELLOW	5.0 [16.40]
MPM6S-FLC-10	9/125 SINGLE MODE OS1	OFNR (RISER) RATED	YELLOW	10.0 [32.81]

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY: FIBER OPTICS			
PRODUCT DESCRIPTION: 6 RIB MPO-M/ FLC			
SIZE: A	FSCM NO.: 43321	DWG. NO.: MPM6S-FLC	REV.: B
SCALE: NONE CAD FILE: MPM6S-FLC.SLDDRW			SHEET 2 OF 2