


Bulk Cable Specification

MTCAD00001-1000F Coaxial Cable

MODEL	PRIMARY PACKAGING	SECONDARY PACKAGING	LENGTH
MTCAD00001-1000F	REEL	SPOOL	1000 FT.



Cable Specification		
ITEM	Component A	
	1C	
Conductors	AWG	28
	Size	7/0.127+/-0.008mm
	Material	Tinned Copper
Insulators	Material	Foam-PE
	Diameter	1.62+/-0.08mm
	Average Thickness	0.55mm
Shielding	Material	Tinned Copper
	Coverage	50(+/-3)*0.10(+/-0.008)mm,95% coverage
Jacket	Material	PVC
	Diameter	2.80+/-0.15mm
	Average Thickness	0.40mm
	Color	RED
Characteristics		
1.Voltage rating:30V 2.Operating Temperature:-10 °C~+80 °C 3.Dielectric strength:500V AC/1min 4.Impedance(1C):75+/-10% Ω 5.Insulation resistance:Foam-PE——Min 100 mega ohms-10m @20 °C 6.Conductor resistance:28AWG——Max 239 ohms/km @20 °C 7.Environment Compliant With:RoHS & REACH.		