


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/19/2021	GUITADAURO



ITEM NUMBER	LENGTH INCHES [MM]
N515P-C13L-15-03F	36.0 ± 0.4 [915 ± 10.0]
N515P-C13L-15-06F	72.0 ± 0.8 [1830 ± 20.0]
N515P-C13L-15-10F	120.0 ± 1.2 [3050 ± 30.0]

NOTES:

- VOLTAGE RATING:
DIELECTRIC VOLTAGE WITHSTAND TEST: 1500V / 1 Sec
CONDUCTOR RESISTANCE ≤ 8.88Ω/1000M
VOLTAGE RATING AC 300V
- CABLE MARKING :
(UL) E135710-F5 SJT 3×14AWG 105°C 300V VW-1
c(UL) SJT 3×2.08 mm² (14AWG) 105°C 300V FT2
- OPTIONAL LABELS:
OPTIONAL LABEL(S) MAY INCLUDE
UL, CURRENT AND/OR WARNING
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH SPEC. PS-0031.
- ALL DIMENSIONS FOR REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936				
	DRAWN BY MVEERAPPAN	10/19/2021		CATEGORY POWER PRODUCTS			
THIRD-ANGLE PROJECTION 	CHECKED BY DFRISIELLO	10/19/2021	PRODUCT DESCRIPTION N5-15P - C13 Left, 15A, 125V				
	APPROVED BY GUITADAURO	10/19/2021	<table border="1"> <tr> <td>SIZE A</td> <td>CAGE CODE 43321</td> <td>ITEM NO. N515P-C13L-15</td> <td>REV. A</td> </tr> </table>	SIZE A	CAGE CODE 43321	ITEM NO. N515P-C13L-15	REV. A
SIZE A	CAGE CODE 43321	ITEM NO. N515P-C13L-15	REV. A				
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SCALE: NONE CAD FILE: N515P-C13L-15.SLDDRW SHEET 1 OF 1				