



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	02/21/2023	GUTTADAURO





ITEM NUMBER	LENGTH INCHES [MM]
N520P-N520R-20-03F	36.0 ± 0.4 [910 ± 10.0]
N520P-N520R-20-06F	72.0 ± 0.8 [1830 ± 20.0]
N520P-N520R-20-10F	120.0 ± 1.2 [3050 ± 30.0]
N520P-N520R-20-15F	180.0 ± 1.6 [4570 ± 40.0]
N520P-N520R-20-25F	300.0 ± 2.0 [7620 ± 50.0]

**NOTES:**

- VOLTAGE RATING:**  
DIELECTRIC VOLTAGE WITHSTAND TEST: 1500V / 1sec  
CONDUCTOR RESISTANCE: ≤ 3.51Ω / 1000m  
VOLTAGE RATING: AC 300V
- CABLE MARKING :**  
(UL) E135710-F5 SJTOW 3X10AWG 105°C 300V VW-1 WATER RESISTANT  
C(UL) SJTOW 3X5.26mm<sup>2</sup> (10AWG) 105°C 300V FT2
- OPTIONAL LABELS:**  
OPTIONAL LABEL(S) MAY INCLUDE  
UL, CURRENT AND/OR WARNING
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH SPEC. PS-0031.**
- ALL DIMENSIONS FOR REFERENCE ONLY.**

**REGULATORY COMPLIANCE:**

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [5]   ANGLES ± 1° .XXX = ± .005 [1.3]	APPROVALS DRAWN BY SREITER CHECKED BY KGLEBOVA APPROVED BY GUTTADAURO	DATE 02/21/2023 02/21/2023 02/21/2023	 an INFINITO brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	THIRD-ANGLE PROJECTION 		
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION <b>N5-20P - N5-20R POWER CORD, 20A, 250V</b>	SCALE: NONE CAD FILE: N520P-N520R-20-XXX.SLDDRW
SIZE <b>A</b>		CAGE CODE <b>43321</b>	ITEM NO. <b>N520P-N520R-20-XXX</b>
SHEET 1 OF 1		REV. <b>A</b>	SHEET 1 OF 1