



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVAL
A	INITIAL RELEASE	07/24/2019	MMARTINEZ

NB14-18-FRK-20F CONTAINS:

- 4 #6 U-TYPE SPEED NUT
- 4 #6 2.0 STAINLESS STEEL PAN HEAD PHILLIPS SHEET METAL SCREW
- 1 120x120mm ALUMINUM MESH FILTER
- 1 120x120x38mm 220/240VAC COOLING FAN 18W

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12 [305] = +1 [25] / -0$ $>12 [305] - 60 [1524] = +2 [51] / -0$ $>60 [1524] - 120 [3048] = +4 [102] / -0$ $>120 [3048] - 300 [7620] = +6 [152] / -0$ $>300 [7620] = +5\% / -0\%$ ALL OTHER DIMENSIONAL TOLERANCES: $.X = .2 [5.08]$ $.XX = .02 [51]$ $.XXX = .005 [13]$	APPROVALS DRAWN BY DZINN	DATE 07/24/2019	 50 HIGH STREET NORTH ANDOVER, MA 01845
	CHECKED BY MMARTINEZ	DATE 07/24/2019	
APPROVED BY MMARTINEZ	DATE 07/24/2019	PRODUCT DESCRIPTION FAN REPL KIT-14/18" ENCL 240VAC	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		COLOR VARIATIONS MAY OCCUR
SIZE A		FSCM NO. 43321	DWG. NO. NB14-18-FRK-20F
SCALE: NONE		CAD FILE: NB14-18-FRK-20F.SLDDRW	REV. A SHEET 1 OF 1