




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	05/30/2023	BPUCHASKI	GUTTADAURO



L6/20P MALE CONNECTOR BLACK



C13 FEMALE CONNECTOR BLACK

SJTOW3X14AWG INDUSTRIAL OUTDOOR CABLE 105°C BLACK

NOTES:

- REFERENCE: VOLTAGE RATING 15A/250V
- APPROVALS: UL APPROVED
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:  
EU ROHS DIRECTIVE (MOST RECENT RELEASED VERSION)

<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE:                  ≤12 [305] = +1 [25] / -0                  &gt;12 [305] ≤60 [1524] = +2 [51] / -0                  &gt;60 [1524] ≤120 [3048] = +4 [102] / -0                  &gt;120 [3048] ≤300 [7620] = +6 [152] / -0                  &gt;300 [7620] = +5% / -0</p> <p>ALL OTHER DIMENSIONAL TOLERANCES:                  .X = ± .2 [5]   FRACTIONS ± 1/32                  .XX = ± .02 [.5]   ANGLES ± 1°                  .XXX = ± .005 [.13]</p> <p>THIRD-ANGLE PROJECTION</p>	APPROVALS	DATE	<p>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</p>	
	DRAWN BY BPUCHASKI	05/30/2023		CATEGORY  <b>POWER CORD</b>
	CHECKED BY DGUST	05/30/2023		
	APPROVED BY GUTTADAURO	05/30/2023		
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION <b>L6-20P/C13, Industrial STJOW Cord, 250V, 15A</b>			
COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. <b>OWL620C13-15</b>	REV. <b>A</b>
SCALE: NONE		CAD FILE: OWL620C13-15.SLDDRW		SHEET 1 OF 1