


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	05/30/2023	BPUCHASKI	GUTTADAURO



NOTES:

1. REFERENCE: VOLTAGE RATING 15A/125V
2. APPROVALS: UL APPROVED
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:
EU ROHS DIRECTIVE (MOST RECENT RELEASED VERSION)

<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0</p> <p>ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]</p> <p>THIRD-ANGLE PROJECTION</p>	APPROVALS	DATE	<p>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</p>
	DRAWN BY BPUCHASKI	05/30/2023	
	CHECKED BY DGUST	05/30/2023	
	APPROVED BY GUTTADAURO	05/30/2023	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		<p>CATEGORY</p> <p>POWER CORD</p>	
COLOR VARIATIONS MAY OCCUR		<p>PRODUCT DESCRIPTION</p> <p>N5-20P/C13, Industrial STJOW Cord, 125V, 15A</p>	
SIZE A	CAGE CODE 43321	ITEM NO. OWN520C13-15	REV. A
SCALE: NONE		CAD FILE: OWN520C13-15.SLDDRW	
			SHEET 1 OF 1