

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	04/11/2023	DZINN	GUTTADAURO

1. CONSTRUCTION:

CONDUCTOR: 12 AWG TINNED COPPER
 INSULATION: POLYVINYLCHLORIDE, .015" NOM. WALL THICKNESS
 INNER JACKET: NYLON, MIN THICKNESS .004"
 JACKET: POLYVINYLCHLORIDE, BLACK, .045" NOM. WALL THICKNESS.
 OVERALL CABLE DIAMETER

NOM. DIA.
 .091"
 .143"
 .155"
 .453±.016"

2. PHYSICAL PROPERTIES:

TEMPERATURE RATING, MAX 90°C
 TEMPERATURE RATING, MIN. -40°C
 JACKET IS UV RESISTANT

3. ELECTRICAL CHARACTERISTICS:

DIELECTRIC STRENGTH (kv/1min) 2.0(AC)
 VOLTAGE RATING, MAX. 600V
 MAX COND D.C. RESISTANCE AT 20°C (W/km) ≤5.64

4. REFERENCE STANDARD:

UL1277 & UL1581 & UL83
 MEETS (UL) VW-1 FLAME TEST

5. MARKING IN WHITE:


E497465 (UL) TYPE TC-ER THHN/THWN 3C 12AWG 90°C DRY/75°C WET
 600V SUN RES VW-1 -40°C JHOSIN



6. CONDUCTOR COLOR:

1. RED
2. BLACK
3. BLUE

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [1.3]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936			
	DRAWN BY DZINN	04/18/2023	CATEGORY			
	CHECKED BY HBAKKE	04/18/2023	BULK CABLE			
	APPROVED BY DGUST	04/18/2023	PRODUCT DESCRIPTION POWER BULK TRAY CABLE, ER, 12AWG, 3C, BLK, 600V, 1KFT			
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. PBTC123	REV. A
		SCALE: NONE	CAD FILE: PBTC123.SLDDRW		SHEET 1 OF 1	