

6

5

4

3

2

1

## REVISION

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	02/06/2024	HBAKKE	GUTTADAURO

F


E

D

C

B

A



## NOTES:

- VOLTAGE RATING:  
DIELECTRIC VOLTAGE WITHSTAND TEST: 1500V/1 SECOND  
CONDUCTOR RESISTANCE:  $\leq 9.05\Omega/1000$  METERS  
CABLE VOLTAGE RATING: AC 600V  
RATING: 125V/15A
- CABLE MARKING:  
WX (NO.515): (ETL)US 3176559 STW 3X14AWG 60°C 600V VW-1  
C(ETL) STW3X2.08mm<sup>2</sup>(14AWG) FT2  
PH (NO.829): (ETL)US 5019033 STW 3X14AWG 60°C 600V VW-1  
C(ETL) STW3X2.08mm<sup>2</sup>(14AWG) FT2
- OPTIONAL LABELS MAY INCLUDE UL, CURRENT AND/OR WARNING.
- CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED.
- ALL DIMENSIONS FOR REFERENCE ONLY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

ITEM NUMBER	LENGTH [TOL.]	
	FEET	METERS
PCI03W4-LED-3FT	3.00 [ $\pm 0.05$ ]	0.91 [ $\pm 0.01$ ]
PCI03W4-LED-6FT	6.00 [ $\pm 0.10$ ]	1.83 [ $\pm 0.03$ ]

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS


TOLERANCES:  
 .X =  $\pm 0.2$  [5]      FRACTIONS  
 .XX =  $\pm 0.02$  [0.5]       $\pm 1/32$   
 .XXX =  $\pm 0.005$  [0.13]      ANGLES  $\pm 1^\circ$

CABLE LENGTH TOLERANCES:  
 $\leq 12$  [305] =  $+1$  [25] / -0  
 $>12$  [305]  $\leq 60$  [1524] =  $+2$  [51] / -0  
 $>60$  [1524]  $\leq 120$  [3048] =  $+4$  [102] / -0  
 $>120$  [3048]  $\leq 300$  [7620] =  $+6$  [152] / -0  
 $>300$  [7620] =  $+5\%$  / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE.  
UN-DIMENSIONED NON-CRITICAL FEATURES  
MAY VARY IN SIZE AND LOCATION  
COLORS MAY VARY

**L-com**  
an INFINIT<sup>®</sup> brand

Website: [www.L-com.com](http://www.L-com.com)  
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND  
TOLERANCES PER ASME Y14.5

SCALE      SHEET  
NONE      1 OF 1

DESCRIPTION  
NEMA 5-15P TO TRIPLE NEMA 5-15R W SPLITTER CABLE, LED CONNECTORS

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	HBAKKE	PCI03W4-LED	A

6

5

4

3

2

1