

6

5

4

3

2

1

F

E

D

C

B

A

F

E


D

C

B

A

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	B	ECO-14311	03/04/2025	TDUFRENE	DGUST


**NOTES:**

- CABLE:
SJT 12AWG 3C 105°C 300V VW-1 JACKET: PVC, BLACK
MARKING (NO.682): (UL) E135710-F5 SJT 3X12AWG 105°C 300V VW-1
C(UL) SJT 3X3.31MM2(12AWG) 105°C 300V FT2
- ELECTRICAL CHARACTERISTICS:
DIELECTRIC VOLTAGE WITHSTAND TEST: 1500V / 1 SEC
CONDUCTOR RESISTANCE $\leq 5.69\Omega/1000M$ AT 20°C
VOLTAGE RATING: AC 300V AT 20°C.
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION).

ITEM NO.	LENGTH	
	METERS [MM]	FT [IN]
PCS02L2-BLK-6F	1.83 [± 30]	6.0 [± 1.18]
PCS02L2-BLK-10F	3.05 [± 30]	10.0 [± 1.18]
PCS02L2-BLK-15F	4.57 [± 30]	15.0 [± 1.18]

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERSTOLERANCES:
X = ± 2 [5]
.XX = ± 0.02 [0.5]
.XXX = ± 0.005 [0.13]
FRACTIONS
 $\pm 1/32$
ANGLES $\pm 1^\circ$ CABLE LENGTH TOLERANCES:
 ≤ 12 [305] = ± 1 [25] / -0
 >12 [305] ≤ 60 [1524] = ± 2 [51] / -0
 >60 [1524] ≤ 120 [3048] = ± 4 [102] / -0
 >120 [3048] ≤ 300 [7620] = ± 6 [152] / -0
 >300 [7620] = $\pm 5\%$ / -0ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE.
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY**L-com**
an INFINIT® brandWebsite: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5SCALE
NONE
SHEET
1 OF 1

DESCRIPTION

N5-15-C19 LA POWER CORD, 15 AMP

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	TDUFRENE	PCS02L2-BLK	B

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE
EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW
PROHIBITED.

6

5

4

3

2

1