





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	02/03/2021	BPUCHASKI



PART NUMBER	LENGTH FEET	LENGTH METERS
PPA00007WH-01F	1.0	.30
PPA00007WH-02F	2.0	.61
PPA00007WH-03F	3.0	.91
PPA00007WH-06F	6.0	1.83
PPA00007WH-08F	8.0	2.44

NOTES:

- VOLTAGE RATING: AC ≥ 1500V/S
- CONNECTOR C13 POWER RATING: 15A UL-E257089
- CONNECTOR C20 POWER RATING: 15A UL-E257089
- CABLE: SJT 14AWGx3, 300V, 60°C VW-1 E313867 FT1
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH SPEC. PS-0031.
- ALL DIMENSIONS FOR REFERENCE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS DRAWN BY BPUCHASKI CHECKED BY DZINN APPROVED BY MBLACKWOOD	DATE 02/03/2021 02/03/2021 02/03/2021	 an INFINIT® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY POWER PRODUCT		PRODUCT DESCRIPTION PC/PDU Power Cord - C20 to C13 - 15Amp
THIRD-ANGLE PROJECTION 	SIZE A	CAGE CODE 43321	ITEM NO. PPA00007WH	REV. A
SCALE: NONE		CAD FILE: PPA00007WH.SLDDRW		SHEET 1 OF 1