




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/11/2021	MBLACKWOOD





C13 JACK
EN60320
BLACK



C14 PLUG
EN60320
RIGHT ANGLE
BLACK

MODEL NO.	LENGTH +/-2%
PPA00021-3F	3.0 FEET
PPA00021-6F	6.0 FEET
PPA00021-10F	10.0 FEET

- NOTES:
1. APPROVALS: UL / CSA OR cUL
 2. RATING: 15A / 250V
 3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS	DATE	 an INFINITI® brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	DRAWN BY DFRISIELLO	01/11/2021			
	CHECKED BY DZINN	01/11/2021	CATEGORY	POWER PRODUCTS	
	APPROVED BY MBLACKWOOD	01/11/2021	PRODUCT DESCRIPTION	CPU/PDU Power Cord - C14 Right Angle to C13 - 15 Amp	
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. PPA00021
SCALE: NONE		CAD FILE: PPA00021.SLDDRW		SHEET 1 OF 1	