



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	05/10/17	J.LABOY



- NOTE:**
- 1- MATERIAL: .06 THICK COLD ROLLED STEEL
 - 2- PANEL FINISH: FLAT BLACK POWDER COAT
 - 3- SILKSCREEN COLOR: WHITE
 - 4- PANEL ASSEMBLY SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0014
- REGULATORY COMPLIANCE:**
CE 2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		50 HIGH STREET NORTH ANDOVER, MA 01845
	DRAWN BY B.PUCHASKI	04/25/17		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3]	CHECKED BY D.FRISIELLO	05/08/17	PRODUCT DESCRIPTION 16 PORT 19" 1U RACK MOUNT W/ CAT6 MINI COUPLERS	
	APPROVED BY M.MARTINEZ	04/25/17	SIZE A FSCM NO. 43321 DWG. NO. PR175C6-16M	REV. A
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SCALE: NONE	CAD FILE: PR175C6-16M.SLDRW	SHEET 1 OF 1