



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	05/10/17	J.LABOY



NOTE:

- 1- MATERIAL: .06 THICK COLD ROLLED STEEL
- 2- PANEL FINISH: FLAT BLACK POWDER COAT
- 3- SILKSCREEN COLOR: WHITE
- 4- PANEL ASSEMBLY SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0014

REGULATORY COMPLIANCE:
CE 2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	APPROVALS DRAWN BY B.PUCHASKI CHECKED BY D.FRISIELLO APPROVED BY M.MARTINEZ	DATE 05/02/17 05/08/17 05/02/17	50 HIGH STREET NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR			CATEGORY RACK/ENCLOSURE PRODUCT DESCRIPTION 32 PORT 19" 2U RACK MOUNT W/ CAT6 SHIELDED MINI COUPLERS
PROJECTION 	SIZE A	FSCM NO. 43321	DWG. NO. PR35C6-32SM	REV. A
SCALE: NONE		CAD FILE: PR35C6-32SM.SLDRW		SHEET 1 OF 1