


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/29/13	D.GRIFFIN
B	ECN 7678: UPDATED CABLE DESCRIPTION	11/12/14	D. CASTRO



NEMA 5/15  
COLOR: BLACK

B

THREE 18AWG CONDUCTORS,  
SVT3X18AWG,  
USA/AC POWER CORD  
COLOR: BLACK

EN60320 C13  
COLOR: BLACK

**NOTES:**

1. RATED 10A/125V
2. UL LISTED, CSA APPROVED
3. CORD TO BE PLACED IN A CLEAR BAG WITH WHITE LABEL: "PN: PSCORD3"
4. CENTER THE LABEL ON THE CLEAR BAG.

BAG LABEL EXAMPLE:

PN: PSCORD3

**REGULATORY COMPLIANCE:**  
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [1.27]	APPROVALS D. DESJARDIN CHECKED BY D. PARHAM APPROVED BY M. MARTINEZ	DATE 8/28/13 8/29/13 8/29/13	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845				
	CATEGORY <b>POWER PRODUCTS</b>			PRODUCT DESCRIPTION <b>CBL PWR N5/15 -C13 18AWG</b>			
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR		SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>PSCORD3</b>
	SCALE: NONE		CAD FILE: PSCORD3.SLDDRW		SHEET 1 OF 1		