

**Bulk Cable Specification**

---

MODEL	PRIMARY PACKAGING	SECONDARY PACKAGING	LENGTH
R1088-100	COIL	BOX	100 FT.
R1088-500	SPOOL	STRETCH WRAP	500 FT.
R1088-1K	SPOOL	STRETCH WRAP	1,000 FT.

75 OHM IMPEDANCE.

TWO STRANDED 25 AWG CENTER CONDUCTORS

SHIELDING: COPPER SPIRAL BRAID

JACKET: HIGH FLEX BLACK PVC.

DC RESISTANCE AT 20°C:           0.15Ω/M (0.046Ω/FT) INNER CONDUCTOR NOMINAL  
  0.04Ω/M (0.012Ω/FT) SHIELD NOMINAL

CAPACITANCE AT 1kHz               59Pf/M (16.8Pf/T)

CHARACTERISTIC IMPEDANCE AT 100MHz: 75Ω±5%

ATTENUATION (10MHz):           0.06Db/M (0.018Db/FT)

NOTE:  
SEE ASSEMBLY INSTRUCTIONS ASI-0026.DOC