


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/23/11	D.GRIFFIN
B	ECN 7267: SHOWED FEMALE CONTACTS, CHANGED NOTES, ADDED WIRE	1/28/14	D. CASTRO
C	ECN 7301: SHOWED 2 CABLES	2/20/14	D. CASTRO



**RA50FF
FEMALE/FEMALE/FEMALE JUMPER**

SOCKET CONTACTS TO BE PHOSPHOR BRONZE GOLD FLASHED OVER NICKEL WITH 30μIN GOLD ON MATING SURFACE

NOTES:

1. THESE JUMPERS USE STANDARD CRIMP & POKE TYPE D-SUBMINIATURE SOCKET CONTACTS.
2. CABLES TO BE BULK PACKAGED 10 PIECES PER BAG.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3]	APPROVALS DRAWN BY D.FRISIELLO	DATE 12/22/11		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	CHECKED BY D.FRISIELLO	DATE 12/22/11		CATEGORY TELECOM/MODULAR		
	APPROVED BY S.SMITH	DATE 12/22/11	PRODUCT DESCRIPTION F/F/F "Y" JUMPER			
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. RA50FF
			SCALE: NONE	CAD FILE: RA50FF.SLDDRW	SHEET 1 OF 1	