


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	03/16/2023	SREITER	AGANWANI



NOTES:

ELECTRICAL DATA:

1. IMPEDANCE: 75Ω
2. FREQUENCY RANGE: DC TO 1GHz

MECHANICAL:



1. BODY: BRASS, NICKEL PLATED
2. CONTACT: BRASS, GOLD PLATED
3. INSULATION: PTFE

ALL DIMENSIONS FOR REFERENCE ONLY.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

**RECOMMENDED
MTG HOLE PATTERN**

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY SREITER	03/16/2023	
	CHECKED BY DWANG	03/29/2023	
	APPROVED BY AGANWANI	03/29/2023	
THIRD-ANGLE PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CATEGORY PCB CONNECTOR	
	COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION 75 ohm F FEMALE BULKHEAD MOUNT CONNECTOR SOLDER ATTACHMENT THRU HOLE PCB, .340 INCH X .091 INCH HOLE SPACING	SIZE A
		CAGE CODE 43321	ITEM NO. RFPCB-F-FS-1G-86
		SCALE: NONE	CAD FILE: RFPCB-F-FS-1G-86.SLDDRW
			SHEET 1 OF 1